


The Centec Group

Centec is a privately owned group of companies. Our automated process skids are used throughout the entire brewing process. For soft drinks, dairy and food industries we offer a large variety of skid mounted systems. We have decades of experience in water purification and deaeration, carbonation, liquid blending and dosing, flash pasteurization and cleaning-in-place. Centec technology includes a range of high precision process sensors for accurately measuring critical product properties such as extract, alcohol, milk fat, O₂ and CO₂. The largest brewery, soft drink, dairy and food groups in the world are among our key customers.



Accuracy. Reliability. Centec.

Germany

Centec GmbH
Wilhelm-Röntgen-Strasse 10
63477 Maintal
Tel.: +49 6181 18 78 0
Fax: +49 6181 18 78 50
info@centec.de

Czech Republic

Centec automatika s.r.o.
Pekařská 8/601
155 00 Praha 5
Tel.: +420 257 084 111
Fax: +420 235 518 701
prodej@centec.cz

USA

Centec LLC
P. O. Box 820
Germantown, WI 53022-0820
Tel.: +1 262 251 8209
Fax: +1 262 251 8376
info@centec-usa.com

UK

Centec UK
Stalworths, The Street
Great Tey, Colchester, Essex, CO6 1JS
Tel.: +44 1206 21 19 21
Fax: +44 1206 21 19 16
info@centec-uk.com

Serbia

Centec Serbia
Bogdana Žerajića 34/III
11000 Beograd
Tel.: + 381 11 358 11 24
Fax: + 381 11 358 11 24
info@centec.rs

India

Centec RRR Systems & Sensors Pvt Ltd
RRR House, Plot 80, Sector 23
Turbhe Naka, Navi Mumbai - 400 705
Tel.: +91 22 2783 3655 & 2783 1348
Fax: +91 22 2783 4814
mail@centecrrr.com

Brazil

Centec América Latina Ltda
Rua Mexico 148 conj. 1004 Centro
20031 142 Rio de Janeiro
Tel.: +55 21 2223 2066
centelatina@terra.com.br

INTRAP

Product Sterile Filtration

Centec Beverage Systems



Automated
process skids
and high precision
sensors from a
single source.
Centec.

INTRAP

The Principle

The Centec trap filter skid INTRAP is a single- or multi-stage system containing back flushable filter cartridges with specific pore sizes. This unit can be used for many applications, e.g. for sterile product filtration or as an early step in a water treatment regime. By sterile filtration, particles and micro-organisms are removed from the product. This leads to an improvement of product stability and shelf life. When water is purified, prior solids removal avoids clogging and damage of the membranes that are subsequently applied to achieve even higher purity. INTRAP can be designed for manual operation with pressure indicators or as a fully automated system. For automatic back flushing the differential pressure needs to be continuously measured. With this option included, the lifetime of the filter cartridges is maximized. Depending on product characteristics, in some processes sterile filtration may be an alternative to flash pasteurization which is eliminating the most harmful micro-organisms by heat. Other manufacturers use sterile filters to treat the product before they flash pasteurize it.

Technical Data

Capacity	20 - 1.500 hl/h
Pressure of Operation	2 - 8 bar
Temperature of Operation	2 - 85 °C
Temperature of CIP	up to 85 °C
Material	1.4301/1.4404 AISI 304/316L
PLC	SIMATIC S7
Options	in-line O ₂ measurement pressure measurement flash pasteurization



The Centec production is certified according to ISO 9001.

- **Application Specific and Energy Efficient**
reliable product sterilization by specific sterile filters
removal of solids to avoid clogging of membranes
automatic back flushing on demand
- **Modular Design with Standard PLC**
skid mounted for easy installation and start-up
- **Hygienic Execution and Full CIP Capability**
- **Outstanding Price-Performance-Ratio**

Experience. Expertise. Centec.

*Ion Exchange · Reverse Osmosis · Membrane Deaeration · Column Deaeration · Hops Pre-Isomerization
Wort Aeration · Yeast Pitching · Nitrogenation · Carbonation · Carboblending · High Gravity Blending
Multi Component Mixing · Additive Dosing · Flash Pasteurization · Cleaning-in-Place · Dealkoholization*

